

## Indobarr 1S PE

Description	Standard	Unit	Values		
Substance	Tappi T410	GSM	225	255	275
Caliper	Tappi T411	µm	349	397	434
Bending resistance (L&W) - MD	Tappi T556	mN	183	302	398
Bending resistance (L&W) - CD	Tappi T556	mN	91	151	199
Bending resistance (L&W) - GM	Tappi T556	mN	129	214	281
Poly substance (back)	Mill method	GSM	15	15	15
Poly adhesion strength	Tappi T539	Points	3	3	3
Surface tension (back)	Tappi T698	Dynes/cm	38	38	38
Roughness - Bendsten (top)	ISO 8791-2	ml/min	50	50	50
Roughness - Bendsten (back)	ISO 8791-2	ml/min	300	300	300
Moisture content	Tappi T412	%	6	6	6
Surface strength IGT pick (top)	ISO 3782 & 3783	m/sec	0.7	0.7	0.7

**FSC® certified**